


Upgrade the performance of Harvard and Filmax LTC filter systems with Velcon Superdri[®] filter cartridges.

Studies have shown that all-cellulose Harvard filter cartridges do not remove moisture in oil over extended periods of time. Quickly saturated, these filters simply allow the circulation of wet oil in the LTC compartment. The Velcon SD-718P3 removes fine carbon and dissolved water for over a year in free breathing LTC compartments. Conversion Kit CK-1483 adapts the Harvard H1000 housing on Harvard and Filmax filter systems to allow use of a Velcon high performance **Superdri** filter, SD-718P3, to improve LTC oil quality and filter system performance.



CK-1483 Plates

The conversion kit consists of two plates. One plate slides over the housing center post and is pressed onto the bottom. The second plate seals the top of the high performance Velcon replacement cartridge.

BENEFITS

- Retards oil oxidation through consistent dissolved water removal
- Maintains high ASTM D-1816 method breakdown voltage
- 0.3 micron filter media removes even the finest carbon particles
- Improves contact resistance to coke formation

ORDERING INFORMATION

- CK-1483
- SD-718P3 **Superdri** filter cartridge



Harvard H1000 Housing